



COOL TO THE CORE // CHILL-ITS® COOLING VESTS



6665
Evaporative Cooling Vest -
Embedded Polymers, Zipper Closure



6667
Wet Evaporative Cooling Vest -
PVA, Zipper Closure



6668
Hi-Vis Safety Cooling Vest -
Type R, Class 2



6685
Dry Evaporative Cooling Vest -
Zipper Closure



6687
Dry Evaporative Cooling Vest -
Elastic Waist



6215
Premium FR Phase Change Cooling Vest
With Rechargeable Ice Packs



6230
Standard Phase Change Cooling Vest With
Rechargeable Ice Packs




6260
Lightweight Phase Change Cooling Vest With
Rechargeable Ice Packs



6210
Phase Change Cooling Ice Vest

COOLING TYPE/ TECHNOLOGY	WET EVAPORATIVE COOLING EMBEDDED POLYMERS	WET EVAPORATIVE COOLING PVA	WET EVAPORATIVE COOLING EMBEDDED POLYMERS	DRY EVAPORATIVE COOLING	DRY EVAPORATIVE COOLING	PHASE CHANGE COOLING	PHASE CHANGE COOLING	PHASE CHANGE COOLING	PHASE CHANGE COOLING
ENVIRONMENT	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/ MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/ MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW/ MODERATE HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW HUMIDITY AND SUFFICIENT AIRFLOW	HOT AND DRY INDOOR + OUTDOOR ENVIRONMENTS WITH LOW HUMIDITY AND SUFFICIENT AIRFLOW	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)	HOT INDOOR + OUTDOOR ENVIRONMENTS (NO AIRFLOW REQUIRED)
HOW TO WEAR	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT	WEAR OVER T-SHIRT
CLOTHING LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER	OUTER LAYER OR UNDER PPE	OUTER LAYER OR UNDER PPE	OUTER LAYER OR UNDER PPE	OUTER LAYER OR UNDER PPE
COOLING HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 72 HOURS	UP TO 72 HOURS	UP TO 4 HOURS	UP TO 4 HOURS	UP TO 2 HOURS	UP TO 2 HOURS
ACTIVATION METHODS	SOAK IN WATER	RUN UNDER WATER	SOAK IN WATER	FILL WITH 13-17OZ (400-500ML) OF WATER	FILL WITH 13.5-15.5OZ (400-450ML) OF WATER	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR	PLACE IN COOLER OF ICE WATER, FREEZER OR REFRIGERATOR
ACTIVATION TIME	2 - 5 MINUTES (MAXIMUM)	1 - 5 MINUTES	2 - 5 MINUTES (MAXIMUM)	IMMEDIATE	IMMEDIATE	10 MINUTES: COOLER OF ICE 15 MINUTES: FREEZER 25 MINUTES: REFRIGERATOR	10 MINUTES: COOLER OF ICE 15 MINUTES: FREEZER 25 MINUTES: REFRIGERATOR	10 MINUTES: COOLER OF ICE 15 MINUTES: FREEZER 25 MINUTES: REFRIGERATOR	10 MINUTES: COOLER OF ICE 2-3 HOURS: FREEZER 5-6 HOURS: REFRIGERATOR
PHASE CHANGE TEMPERATURE	--	--	--	--	--	64°F // 18°C	64°F // 18°C	64°F // 18°C	64°F // 18°C
STANDARDS/COMPLIANCE	--	--	ANSI/ISEA 107-2020 TYPE 2, CLASS R	--	--	VEST/FABRIC: ASTM F1506 ATPV RATING CAT 1	--	--	--
POCKETS	--	--	1 CHEST EXTERIOR POCKET 2 LOWER INTERIOR POCKETS PEN POCKET	--	--	PEN POCKET	--	2 LOWER EXTERIOR POCKETS	--
CLOSURE	ZIPPER	ZIPPER	ZIPPER	ZIPPER	HOOK & LOOP	HOOK & LOOP	HOOK & LOOP	ZIPPER	BUCKLE WAIST, HOOK & LOOP SHOULDER STRAPS
REFLECTIVE ACCENTS	--	--	YES	--	--	YES	--	--	--
COLOR	HI-VIS LIME OR GRAY	BLUE	HI-VIS LIME	HI-VIS LIME	HI-VIS LIME	HI-VIS ORANGE OR TAN	TAN	BLACK	CLEAR
SIZING (CHEST CIRCUMFERENCE)	M: 36-38IN (91-97CM) L: 38-42IN (97-107CM) XL: 42-45IN (107-117CM) 2XL: 46-50IN (117-127CM) 3XL: 50-54IN (127-137CM)	M: 39IN (100CM) L: 42IN (107CM) XL: 45IN (114CM) 2XL: 48IN (122CM) 3XL: 51IN (130CM) 4XL: 54IN (137CM) 5XL: 57IN (145CM)	S: 45IN (114CM) M: 50IN (127CM) L: 55IN (140CM) XL: 60IN (152CM) 2XL: 65IN (165CM)	M: 38-41IN (97-104CM) L: 41-44IN (104-112CM) XL: 44-47IN (112-119CM) 2XL: 47-50IN (119-127CM) 3XL: 50-53IN (127-135CM) 4XL: 53-56IN (135-142CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 32-40IN (81-102CM) L/XL: 40-52IN (102-132CM)	S/M: 30IN (78CM) L/XL: 33IN (84CM) 2XL/3XL: 34.5IN (87CM)	ONE SIZE
CARE INSTRUCTIONS	HAND WASH & HANG DRY	MACHINE WASH & HANG DRY	HAND WASH & HANG DRY	MACHINE WASH & HANG DRY	MACHINE WASH & HANG DRY	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH	VEST: MACHINE WASH & HANG DRY PACKS: HAND WASH	HAND WASH WITH MILD DETERGENT & WARM WATER, TOWEL DRY
CUSTOM LOGO	--	YES	--	--	--	--	--	YES	--



6667



6687



6215

LEARN THE DIFFERENCE BETWEEN COOLING
TECHNOLOGIES AT [ERGO.ZONE/COOLINGTECH](https://ergo.zone/coolingtech)